



Providing a targeted approach to strategic technology implementation.

Iatric® MobiLab® Desktop Hardware Options

When using MobiLab® Desktop SE you will have several printer options. Your site's workflow will dictate which printer or combination of printers will be needed for the application. Below is a breakdown of the most commonly used printers in the desktop application.

MobiLab® Printers

Zebra ZQ610 Mobile Printer

Many sites use the Zebra ZQ610 as a USB printer on carts or in locations where the printer is mounted on the wall. There are three options for this printer:

A. The printer can be used as a USB only printer. Purchasing a printer without the wireless card will reduce costs, allow you to use the same labels as the mobile option and have a durable printer that can be wall

mounted. This version of this printer is not interchangeable or able to be swapped out with the mobile wireless version of the printer since it does not have a wireless card. Lastly, the USB does not have power over USB so you are still required to swap batteries or plug the printer into an AC supply. This printer is often wall mounted or placed in a cabinet. In other scenarios, the printer can be installed on carts when a printer is dedicated to each cart.

B. In many emergency departments, the USB printer is both USB and AC power wired. This is the same configuration as the printer above with the exception of the need to recharge batteries.

C. In other layouts, the wireless version of the printer is placed at nursing stations or other central locations for staff to use the printer and return it after use. This is one of the more common configurations in low draw areas. Many sites will include one or two printers at each nursing station with a spare battery being charged to be swapped out as needed. This allows you to purchase and maintain one printer throughout the facility to maintain and troubleshoot.



Zebra ZD410

A wired USB AC power low-end Zebra printer can also be used in the desktop application.

This is a low-cost option and often used in sites where a printer is placed in every patient room at every desktop computer. The downside of this printer is that it is not durable and requires a separate roll of labels than the QLn printers. This printer is generally only used for sites with a very large number of printers and in cases of printers in every room hospital wide.



AUTHORIZED FULL SERVICE PROVIDER